
THE NEXUS SYSTEM[™] ADVANTAGE

Though solid systems may provide similar conveniences, performance is where Nexus has them beat! The Nexus System[™] consists of highly concentrated laundry products that provide the most accurate and dependable product dispensing available to institutional on-premis laundries. Through the use of precise peristaltic pumps, product use rates can be set and maintained with only periodic maintenance. Peristaltic pumping systems consistently deliver the accurate results that you expect.



Testing has proven that solid laundry dispensing units are highly dependent on water feed temperatures, water feed pressures and capsule levels to maintain proper use rates and results. As depicted in the graphs above, as temperature, pressure and fill levels change, so does the amount of product being dispensed which affects not only costs but results as well. The Nexus System[™] is not affected by these variables and delivers the exact use rate for maximum results.

DELIVERY CAP SET UP





Remove shipping cap from product. Position the delivery cap onto the product and push down firmly in the center.





tight. Position the barb towards its and move side to side to release. connection tubing.

While pushing down, screw the cap TO REMOVE: Unscrew the white ring



There are two different delivery caps available for use with the Nexus System. The instructions for set up are the same for both delivery caps.

- ANGLED BARB CONNECTION CAP (5722491)
- STRAIGHT BARB CONNECTION CAP (6081606)









now percent to freeh air and keep conflictable for break AT FIRST ALD. INEMEDIATELY CALL & POSSON CON TOTALS. EXECUTION TO CONTRACT, AND ATTACKS



USChemical 316 HART STREET • WATERTOWN, WI 53094 (800) 558-9566

WWW.USCHEMICAL.COM

© U.S.CHEMICAL 2015

PERFORMANCE OF NEXUS SYSTEM™ VS TYPICAL SYSTEMS



US Chemical



COMBINING THE PERFORMANCE OF LIQUIDS WITH THE CONVENIENCE OF SOLIDS

EASY TO HANDLE



The Nexus System[™] was designed to take the pain out of replacing product containers. Lightweight canisters replace bulky 5 gallon pails and feature specially designed hand grips molded into the canister for easy handling.

SAFE TO USE



With TED[™] (Totally Enclosed Dispensing), Nexus System eliminates accidental spills and splashes when changing chemicals. The specially designed capping system only allows product to be dispensed when the canister is in the dispenser, providing a barrier between the product and operator.

COMPACT DESIGN





With its compact canister design, Nexus System requires less storage space than other systems. Docking stations are wall mounted and require no floor space, making the area around laundry machines more accessible.

REDUCES SOLID WASTE



Nexus System products contain highly concentrated formulas that allow for smaller canister sizes. One concentrated canister of product is equal to a typical 5 gallon pail. Using the Nexus System reduces the amount of plastic waste your operation generates from laundry containers by up to 60% or more!



SUDS 🦗

EXCEPTION EXCEPT

-

BCYIN (

BREAK

Nexus[™] Break is a hyper-concentrated alkaline builder that contains water conditioners and iron inhibitors. This unique formula provides great grease fighting ability while handling the toughest water conditions including high iron levels.

2/3100 mL (4284178)

SUDS

Nexus[™] Suds is a hyper-concentrated formula with a blend of quality detergent surfactants. It provides excellent emulsification of soils and prevents redepositing onto fabrics. Designed for use in all water conditions. Suds exhibits outstanding cleaning ability at extremely low use rates.

2/3100 mL (4284135)

ENZYME SUDS EC

Nexus[™] Enzyme Suds EC is an enzyme detergent formulated without harsh builders or solvents. Neutral pH, biodegradable surfactants and enzymes make this product gentle on fabrics and on the environment. DfE approved. Recognized for safer chemistry. www.epa.gov/dfe



OXYGEN BLEACH

Nexus[™] Oxygen Bleach is a versatile product that provides excellent cleaning ability while still being safe to use on colored and synthetic fabrics. Nexus[™] Oxygen Bleach aids in the overall success of today's complicated laundry programs.

SOUR/SOFT

Nexus[™] Sour/Soft is a hyper-concentrated formula that provides effective and economical results where a combination sour and softener is preferred. This unique sour/soft combination inhibits iron deposits, reducing the need for separate products. Formulated with optical brighteners.

2/3100 mL (4284311)





2/3100 mL (5120845)





Nexus[™] Built Detergent is a hyperconcentrated formula featuring highly active laundry builders and superior quality surfactants. Designed for all soil and water conditions, including high iron levels, Nexus[™] Built Detergent offers unmatched levels of performance, convenience and low use cost.

2/3100 mL (4284215)

SUDS EC

Nexus[™] Suds EC is a highly active surfactant based laundry detergent that rapidly biodegrades in the environment. This formula provides excellent emulsification of soils and prevents redepositing onto fabrics. DfE approved. Recognized for safer chemistry. www.epa.gov/dfe

2/3100 mL (5110840)



SOFTENER

Nexus[™] Softener is a hyper-concentrated formula that provides the most effective and economical results in applications where a separate softener is preferred. This product may be used with or without Nexus[™] Sour, providing the flexibility needed in many institutional laundry settings.

2/3100 mL (4284240)

SOUR

Nexus[™] Sour is a hyper-concentrated formula that provides the most effective and economical results in applications where a separate sour is preferred. It provides effective pH control, eliminates iron stains and prevents yellowing on all types of fabric. This product may be used with or without Nexus[™] Softener.

2/3100 mL (4284282)

DESTAINER

Nexus[™] Destainer is the highest quality concentration of liquid chlorinated destainer available for use in institutional laundries. It is produced to stringent manufacturing controls, ensuring the highest available chlorine content and maximum shelf life. This product may be wall mounted with optional wall bracket in conjunction with the Nexus[™] docking station.

2.5 gal (077231)





AND A DECK

