



MECHANICAL WAREWASH DETERGENT LP



FEATURES

- High alkaline
- Concentrated
- Excellent water conditioning

BENEFITS

- Removes tough, burned-on soil
- Efficient and economical
- Can be used in all water hardness conditions

RECOMMENDED USES

For Institutional Use Only. DO NOT USE ON ALUMINUM OR ANY SOFT OR PRECIOUS METALS.

SPECIFICATIONS

Color :	Red	pH use dilution :	11.0-12.5	Phosphorus content :	0.46%
Scent/Odor :	None added/Amine	Approvals :	cRc		
Character :	Clear, non-viscous liquid				
Foam :	Non-foamer				

IMPORTANT

Read and understand the label and Safety Data Sheet (SDS). These provide a description of hazards, precautions, personal protective equipment, first aid, 24 Hour Emergency lines, storage data and other safe handling information. The SDS is provided with each container shipped. It is also available on our website or from the distributor.

PRODUCT DIRECTIONS

EQUIPMENT TO USE

Automatic warewash dispensing system.

DIRECTIONS TO USE

USE DILUTION: Concentration varies due to environmental conditions. Your sanitation specialist will adjust properly to meet your needs.

FOR LOW TEMPERATURE WAREWASHING: 1. Pre-flush and/or scrape dishes before washing. 2. Rack dishes properly. Place dishes in machine. 3. Wash using this product. 4. In rinse cycle, use a recommended rinse additive. 5. Sanitize using an approved chlorinated sanitizer at 50 ppm. Test using chlorine test papers or a liquid chlorine test kit. 6. Allow dishes to air dry.

FOR HIGH TEMPERATURE WAREWASHING: 1. Pre-flush and/or scrape dishes before washing. 2. Rack dishes properly. Place dishes in machine. 3. Wash using this product. Maintain wash temperature at 150°-160°F. 4. In rinse cycle, use a recommended rinse additive. Maintain rinse temperature at 180°-190°F. 5. Allow dishes to air dry. Do not use on aluminum.

PACKAGING

This product is available in 2/1.5 gallon bottles (5941521).

