

Ultra Active® Sour 'n Soft is a concentrated combination product. U^a Sour n' Soft contains the highest quality souring agents, fabric softeners, and optical brighteners to leave linen fresh, clean, bright and soft.

Specifications	
Color	Blue
Scent/Odor	Floral
Character	Opaque, non-viscous liquid
Foam	Low
pH Use Dilution	5.5 - 6.5
Phosphorus Content	not over 5.6%
Water Temperature	All
Approvals	None



Pack Sizes	
064855	1/2.5 gallon

Directions For Use

Equipment: Recommended automatic liquid laundry dispensing system.

Use Dilution: Concentration varies due to environmental conditions. Your sanitation specialist will adjust properly to meet your needs.

- 1. Pre-sort laundry prior to wash.
- 2. Pre-soak and/or pre-spot laundry when necessary.
- 3. Place proper amount of soiled linen into laundry machine.
- 4. In wash cycle, inject Ultra Active @ break and Ultra Active @ suds or Ultra Active @ suds+.
- 5. When bleaching, inject Ultra Active® destainer+.
- 6. When souring and softening, inject this product.
- A final pH of 5.5-6.5 is recommended for the linen.

*This product can be used in all water temperatures. Your Chemical Specialist will adjust product concentrations based on results.

Product SDS



Scan the QR code with your mobile device to view the SDS for this product!

Safety Reminder

Read and understand the label and Safety Data Sheet (SDS). These provide a description of hazards, precautions, personal protective equipment, first aid, 24 Hour Emergency lines, storage data and other safe handling information. The SDS is available on our website at www.uschemical.com and is also available by scanning the QR code on the label.