



7 SOUR

Ultra Active® Sour is a concentrated separate laundry sour. Its highly efficient souring agents will neutralize alkaline residues from detergents and water supply. U^a Sour removes rust while preventing fabric harshness and excessive wearing and browning of fabric during ironing.

Specifications

Color	Green
Scent/Odor	Pungent (none added)
Character	Clear, non-viscous liquid
Foam	Non-Foamer
pH Use Dilution	5.5 - 6.5
Phosphorus Content	0.0%
Water Temperature	All
Approvals	cRc



Pack Sizes

064860	1/2.5 gallon
--------	--------------

Directions For Use

Equipment: Recommended automatic liquid laundry dispensing system.

Use Dilution: Concentration varies due to environmental conditions. Your sanitation specialist will adjust properly to meet your needs.

1. Pre-sort laundry prior to wash.
 2. Pre-soak and/or pre-spot laundry when necessary.
 3. Place proper amount of soiled fabric into laundry machine.
 4. In wash cycle, inject U^a break and U^a suds or U^a suds+.
 5. When bleaching, inject U^a destainer+ into the laundry machine.
 6. In final rinse cycle, inject U^a sour and U^a softener.
- A final pH of 5.5-6.5 is recommended for the fabric.

*This product can be used in all water temperatures. Your Chemical Specialist will adjust product concentrations based on results.

Product SDS



Scan the QR code with your mobile device to view the SDS for this product!

Safety Reminder

Read and understand the label and Safety Data Sheet (SDS). These provide a description of hazards, precautions, personal protective equipment, first aid, 24 Hour Emergency lines, storage data and other safe handling information. The SDS is available on our website at www.uschemical.com and is also available by scanning the QR code on the label.