

Clinging Delimer

A Ready-To-Use Descaler



Clinging Delimer is a fast acting foaming descaler for institutional use only. Recommended for use only on stainless steel.

Specifications

Color	Light red
Scent/Odor	None added
Character	Clear, non-viscous liquid
Foam	High
pH Use Dilution	Less than 2.0
Phosphorus Content	2.8%
Approvals	cRc, RBS

Pack Sizes

100832708	6/1 quart case
------------------	----------------



Directions For Use

Equipment: Trigger sprayer, sponge, cleaning cloth, paper towels.

NOTE: AVOID FUMES WHEN USING THIS PRODUCT.

1. Make sure dishmachine is off.
2. Point sprayer directly onto surface to be descaled. Hold nozzle 8-10 inches from surface.
3. Spray over interior surface. Allow foam to work 10-15 minutes.
4. Spray area with clean water and insure the dish tank is drained and cleaned prior to use.
5. Wipe clean with wet cloth, sponge or paper towels. Be sure all foam is removed. Rinse.
6. Repeat if necessary. Do not use on aluminum.

Product Demo



Scan the QR code with your mobile device to view an instructional video featuring this product!

Safety Reminder

Read and understand the label and Safety Data Sheet (SDS). These provide a description of hazards, precautions, personal protective equipment, first aid, 24 Hour Emergency lines, storage data and other safe handling information. The SDS is available on our website at www.uschemical.com and is also available by scanning the QR code on the label.

